





COLLARS
VARIABLE SIZES

Job #:

Item #:

Quantity:

MOUNTING	HANDING	TYPE	SIZE	OTHER



SPECIFICATIONS

COLLARS: Collars are fabricated of type 304 #22 ga stainless steel with a removable vinyl protective coating. All collars have a #4 satin finish to match cabinet. Collars are formed to fit snugly under 1/4" return of cabinet. There will be no visible seams on the vertical sections of the collars. Two pieces are joined and spot welded to form a one piece construction. After unit is installed, collars cannot be removed.

The following is an example how to size collars.

Overall size of cabinet: 17 1/4"W x 54"H x 6 1/4"D

Semi-Recessed collar: C17542 (S2) 4" wall depth

Semi-Recessed collar: C17544 (S4) 2" wall depth

Surface Mounted collar: C17546 (SM)

Drop all fractions to create collar model number

Unit Size Qty.

INSTALLATION

If a semi-recessed collar is required provide a wall opening for that unit at the desired or specified location. Lay unit face down being careful not to scratch cabinet face. Remove vinyl coating from collar. Slide the collar down over the back of the cabinet. If unit is Semi-Recessed, place in wall opening and secure with proper fasteners per application. If surface mounted, install collar the same then place unit on wall opening making sure unit is level and transfer mounting points. Drill pilot holes and secure with proper fasteners per application.

NOTES